

MADE IN THE U.S.A.





See Diagram

39 Gal.

81 Gal.

57.8 lbs.

142 lbs. 36.5 ft.<sup>3</sup> Standard


Premier

forma® Collection Specifications

**HE5527** 

MicroSilk<sup>®</sup>- AirMasseur<sup>®</sup>

DROP IN HOLE SIZE



Faucetry Deck Flat Dimensions

Patents received or pending

of the bath

Drop-in-Hole Size:
Operating Capacity:
Overflow Capacity:
Floor Loading / sq.ft.
Carton Wt.:
Cube:

Note: Equipment may extend

beyond the outside perimeter

Consult factory for details.

Includes Linear Overflow Drain Assembly

6

6

JASON.

IASON.

32

Note: Dimensional Tolerances: +1/4"

Signature	A A A A A A A A A A A A A A A A A A A
Signe	

A 120V system that includes a MicroSilk® unit; a 1HP, variable speed air blower with integral air heater; automatic purge cycle; an electronic control that operated the Micro-Silk® unit, blower, and blower speed for continuous, pulse or wave massage modes; and a 20-minute timer.

A 120V system that includes a MicroSilk® unit; a 1HP, variable speed air blower with integral air heater; automatic purge cycle; (2) Chromatherapy mood lights; Automatic Ozone System; an electronic control that operates the MicroSilk® Unit, blower and blower speed for continuous, pulse or wave massage modes; and a 20-minute timer.

A 120V system that includes a MicroSilk<sup>®</sup> unit; a 1HP, variable speed air blower with integral air heater; automatic purge cycle; (2) Chromatherapy mood lights; Automatic Ozone System; a digital control with LCD display; low water level and temperature sensors; enhanced user control options; a 20-minute timer; and Bluetooth Sound Immersion

Construction: Fiberglass reinforced acrylic bath with Level Form<sup>™</sup> full-support base.

We provide products listed with Intertek ETL SEMKO (Edison Testing Laboratories) U.S. and Canadian and with International Association of Plumbing and Mechanical Officials (IAPMO). Consult factory with your listing requirements.

speed, water temperature and time remaining. Copyright © 2019 Jason International. forma® Collection

System. Control keypad operates the MicroSilk<sup>®</sup> unit, blower and blower speed for continuous,

pulse or wave massage modes, LED Chromatherapy lights and shows MicroSilk® status, blower