

**OPTIONS**

**Flush Volume**

- 1.6 gpf (6.0 Lpf) (1.6)
- 3.5 gpf (13.2 Lpf) (3.5)
- 1.28 gpf (4.8 Lpf) (1.28)
- 6.5 gpf (24.6 Lpf) (6.5)

**Finish**

- Polished Chrome (CP)
- Brushed Stainless (SF)

**Water Efficiency**

- Low Consumption
- Water Saver
- High Efficiency

**Handle**

- Sanigard® (SG)

**Control Stop**

- Adjustable Ground Joint (ADJ/GJ)
- Less (L/STOP)

**Vacuum Breaker**

- Offset (O)

**Offset**

- 2" (51mm) (2-OFST)
- 1" (25mm) (1-OFST)
- 1 ½" (38mm) (1-1/2-OFST)

**Fitting**

- F31AA (F31AA)

**Compliances & Certifications**

- BAA Compliant
- UPC Certified
- cUPC Certified

**NOTES**

For product line drawings, [view model-specific spec sheets](#).

All information contained within this document subject to change without notice.



**DESCRIPTION**

Royal® Exposed Manual Water Closet Bedpan Washer Flushometer

**FEATURES**

- Exposed water closet, diaphragm model Flushometer is intended for floor-mounted or wall-hung top spud bowls
- Operates by means of a metal oscillating, non-hold-open handle with a triple seal handle packing to ensure water conservation
- Presents a leaner, more aesthetic installation, reducing possible bacteria growth on hidden and hard-to-reach surfaces found on other bedpan washer units
- Eliminates the need for unsanitary hose sprays, as well as the additional housekeeping that hoses require and the potential for patient slippage
- Valve body, stop body, diverter body and diverter pivot made from brass casting using semi-red brass for durability and long life
- PERMEX synthetic rubber diaphragm with Dual Filtered Fixed Bypass
- Valve body, Cover, Tailpiece and Control Stop shall be in compliance with ASTM Alloy Classification for Semi-Red Brass
- Valve shall be in compliance to the applicable sections of ASSE 1037.

**DOWNLOADS**

- [Slimline Royal/Regal XL Exposed Installation Instructions](#)
- [Slimline Bedpan Washer Repair and Maintenance Guide](#)
- [Additional Downloads](#)